




PANEL CUTOUT



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR	INTERIOR
RJ 45	CAT 5 JACK	CAT 5 JACK

PICK RATINGS
VOLTS 115V
AMPS 3A
SCCR 10KA
NEMA/VOL 4, 4X, 12

BODY	EPDXY COATED DIE CAST ALUMINUM
GASKET	THERMOPLASTIC ELASTOMER
HANDLE	POLYAMIDE
LEVERS	STAINLESS STEEL

ZP-PSA-32-400

Units: inches [mm]  
Scale: Full

ZP-PSA-32-400

AUTOMATIONDIRECT<sup>®</sup>  
com