




PANEL CUTOUT



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR	INTERIOR
ALL D-SUBS	FEMALE	MALE

PICK RATINGS	
VOLTS	115V
AMPS	3A
SCCR	10KA
NEMA VUL	4, 4X, 12

BODY	EPDXY COATED DIE CAST ALUMINUM
GASKET	THERMOPLASTIC ELASTOMER
HANDLE	POLYAMIDE
LEVERS	STAINLESS STEEL

ZP-PSA-32-300

Units: inches [mm]

Scale: Full

ZP-PSA-32-300