




PANEL CUTOOUT



For power connector, crimp terminals are supplied for hot and neutral connection. Ground wire supplied with an M3 ring terminal applied to end of 6' ground lead.

STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED			
CONNECTION TYPE	EXTERIOR	INTERIOR	
ALL D-SUBS	FEMALE	MALE	

PICK RATINGS	BODY	EPDXY COATED DIE CAST ALUMINUM
VOLTS 115V	GASKET	THERMOPLASTIC ELASTOMER
AMPS 15A	HANDLE	POLYAMIDE
SCCR 10KA	LEVERS	STAINLESS STEEL
NEMA VUL 4,4X,12		

ZP-PSA-16-100

Units: inches [mm]
Scale: Full

ZP-PSA-16-100

AUTOMATIONDIRECT.com