



PICK RATINGS	BODY
VOLTS 115V	EPDXY COATED DIE CAST ALUMINUM
AMPS 3A	GASKET THERMOPLASTIC ELASTOMER
SCSR 10KA	HANDLE POLYAMIDE
NEHA\UL 4,4X,12	LEVERS STAINLESS STEEL

STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED		
CONNECTION TYPE	EXTERIOR	INTERIOR
RJ 45	CAT 5 JACK	CAT 5 JACK

ZP-PDA-32-301

Units: inches [mm]
Scale: Full

ZP-PDA-32-301