




PANEL CUTOUT



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR	INTERIOR
ALL D-SUBS	FEMALE	MALE
RJ 45	CAT 5 JACK	CAT 5 JACK

PICK RATINGS

VOLTS	115V
AMPS	3A
SCCR	10KA
NEMA VUL	4,4X,12

BODY

EPDXY COATED DIE CAST ALUMINUM

GASKET

THERMOPLASTIC ELASTOMER

HANDLE

POLYAMIDE

LEVERS

STAINLESS STEEL

ZP-PDA-32-300

Units: inches [mm]

Scale: Full

ZP-PDA-32-300