



USB TYPE B FEMALE
TD TYPE A FEMALE



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR	INTERIOR
ALL D-SUBS	FEMALE	MALE

PICK RATINGS
VOLTS 115V
AMPS 3A
SCCR 10KA
NEMA VUL 4, 4X, 12

BODY	EPDXY COATED DIE CAST ALUMINUM
GASKET	THERMOPLASTIC ELASTOMER
HANDLE	POLYAMIDE
LEVERS	STAINLESS STEEL

ZP-PDA-32-302

Units: inches [mm]
Scale: Full

ZP-PDA-32-302

AUTOMATIONDIRECT.com