



For power connector, crimp terminals are supplied for hot and neutral connection. Ground wire supplied with an M3 ring terminal applied to end of 6" ground lead.

STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED		
CONNECTION TYPE	EXTERIOR	INTERIOR
ALL D-SUBS	FEMALE	MALE

PICK RATINGS	
VOLTS	115V
AMPS	15A
SCORE	10KA
NEMA VUL	4, 4X, 12

BODY	EPDXY COATED DIE CAST ALUMINUM
GASKET	THERMOPLASTIC ELASTOMER
HANDLE	POLYAMIDE
LEVERS	STAINLESS STEEL

ZP-PSA-24-100

Units: inches [mm]  
Scale: Full

ZP-PSA-24-100