
POLYCARBONATE
VERSION ONLY

FILE #E65324
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory (modshop@hammfg.com) for quotes
Solid models of this enclosure available in .stp or .x_t
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

NOTE
<p>Purchased assembly includes box, lid, 4 cover screws, and preformed silicone gasket.</p> <p>General Purpose ABS version is not UL approved. (Matl UL94 - HB)</p> <p>Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)</p>
Recommended Cover screw torque -- 43-57 ozf-in (30-40 cN-m)

1555W	
1555W Regular Enclosure	
General Purpose ABS RAL-7035	1555WGY
Polycarbonate RAL-7035	1555W2GY
ACCESSORIES	
Steel Inner Panels	1554WPL
Steel Panel / P.C. Board Screw [M3-0.5 x 8mm Plated] (Pkg 100)	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated] (Pkg 100)	1598ATS100
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50
Silicone Pre-formed Gasket Black (Pkg 2)	1554WGASKET



Dimensions:
mm
[inches]