




A = EMITTER AXIS  
B = RECEIVER AXIS



ISOMETRIC VIEW

NOTES:

- 1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
- 2. DIMENSIONS DO NOT IMPLY TOLERANCE.

LHR-M18MA-PMS-603
Units: mm [inches] Scale: Full CONTRINEX PHOTOELECTRIC SENSOR, TUBULAR, THREADED, STAINLESS STEEL, DIFFUSE WITH BACKGROUND SUPPRESSION, 10-250MM SENSING DISTANCE, COMPLEMENTARY LIGHT- ON/DARK-ON, PNP, POTENTIOMETER, 700 HZ SWITCHING FREQUENCY, 4-PIN M12 QUICK- DISCONNECT.
 <b>AUTOMATIONDIRECT</b> .com