



PROSENSE INDUCTIVE PROXIMITY SENSOR, TUBULAR, 8MM DIAMETER X 45MM BODY, STAINLESS STEEL HOUSING, NPN, N.O. OUTPUT, 3MM SENSING DISTANCE, SEMI-FLUSH, 250 HZ SWITCHING FREQUENCY, IP65 IP66 IP67 IP68 IP69K, 3-PIN M8 QUICK-DISCONNECT.

PEW2-AN-3F

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE: **mm**
[inch]

MODEL
REV.

0

DRAWING DATE
3/12/2025

SHEET 1 OF 1