

544.60 mm
[21.441 in]

413.79 mm
[16.291 in]

6.30 mm
[0.248 in]

88.20 mm
[3.472 in]

177.80 mm
[7.000 in]

177.80 mm
[7.000 in]

88.20 mm
[3.472 in]

10 X \varnothing 0.160 in ∇ 0.07 in
 \sphericalangle \varnothing 0.256 in X 82°

3.18 mm TYP
[0.125 in]

8.38 mm TYP
[0.330 in]

9.47 mm
[0.373 in]

95.82 mm
[3.772 in]


203.20 mm
[8.000 in]

95.82 mm
[3.772 in]

1.80 mm
[0.071 in]

TOP VIEW

FRONT VIEW



ISOMETRIC VIEW

Solid models of this enclosure available in STEP or IGES.

RM1922BKSP

Panel Material - .064" Aluminum (5052-H32)

Colour - Black Powder Coat