




SECTION LL-LL



ASSEMBLY - VIEW FROM TOP

HANDLE  
MOUNTING  
HOLES


R3.18 mm  
[0.125 in]

88.13 mm  
[3.470 in]

SECTION MM-MM


330.20 mm  
[13.000 in]

ASSEMBLY - VIEW FROM SIDE



ASSEMBLY - VIEW FROM FRONT

Solid models of this enclosure available in STEP or IGES.



RM2U1913VBK	
Extruded Aluminum Frame - Type 6063	
2 Panels - .064" Aluminum (5052-H32) Powder Coat	
2 Mounting Brackets - .125" Aluminum	
16 Screws - Flat Head 4-40 x 3/8"	
8 Screws - Counter Sunk Head 6-32 x 3/8"	
4 Screws - Counter Sunk Head 10-32 x 3/8"	
16 Nuts - #4 Speed Nuts	
Four Self Adhesive Rubber Feet - 1421T3	
ACCESSORIES	
PULL HANDLES	1427E1BK



**HAMMOND**  
MANUFACTURING™

**RM2U1913VBK**

www.hammondmfg.com