


CUTOUT TEMPLATE VIEWED FROM INSIDE ENCLOSURE. FLIP IF APPLIED TO OUTSIDE OF ENCLOSURE.

TE40-050-24D-4X	
Units:	inches [mm]
Scale:	Full
ENCLOSURE HEAT EXCHANGER, 4887 BTU/H, 24VDC, SIDE MOUNT, 304 SS FOR UL TYPE 4X ENCLOSURE	
 AUTOMATIONDIRECT.com	