



THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED. UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2017 ROBROY ENCLOSURES

**SPECIAL REQUIREMENTS**

ASSEMBLY:

1. (1) POLYCARBONATE ACCESSORY KIT (WPPCACOKIT) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE

HARDWARE INCLUDED:

- (4) #14-20 x 1/2 FLAT HEAD PHILLIPS MACHINE SCREW (RMSC1/4-20X.5FLPH)
- (4) #10-32 x 5/8 PAN HEAD PHILLIPS MACHINE SCREW (RMSC10/32X5/8SS)
- (4) #10-32 x 3/8 PAN HEAD SCREW (RMSC10/32X3/8ZN)
- (4) #10 WASHER (RMWAS10ZN)

2. (1) STYROFOAM SHEET SHALL BE PLACED ON TOP OF COVER INSIDE CARTON

NEMA 250: TYPE 1, 3R, 4, 4X, 6P, 12 IEC 60529: IP66, IP68				STANDARD P/N: AH10106C		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03		.XXX ± 0.010	
COLOR: N/A COLOR STANDARD: PANTONE 7541 C				CUSTOMER DWG:		<div><div>AttaBox™</div><div>Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378</div></div>							
MATERIAL: POLYCARBONATE													
REVISION HISTORY													
REV	DESCRIPTION			DATE	ENG								
-	-			-	-	<div><div>WWW.ATTABOX.COM</div><div>DRAWN BY DATE DRH 06/08/17</div><div>CUSTOMER</div><div>DWG AH10106C</div></div>							
-	-			-	-								
-	-			-	-								
-	-			-	-								
-	-			-	-								
-	-			-	-	SCALE							
DO NOT SCALE						DESCRIPTION STANDARD ENCLOSURE			PART NUMBER ATAH10106C				



**Robroy Enclosures**  
500 Maple Street  
Belding, Michigan 48809  
Phone: 616-794-0700  
Fax: 616-749-3378