



- NOTES:**
- 1. PANEL SHALL BE FREE FROM BURRS & SHARP EDGES
 - 2. PANEL SHALL BE FLAT
 - 3. MISALIGNED EDGES EXCEEDING 0.005" (STEPS) SHALL NOT BE PERMITTED
 - 4. ALL EDGES SHALL BE SQUARE AND PARALLEL
 - 5. PANEL SHALL HAVE CLEAR PVC FILM ON ONE SIDE
 - 6. ALL "2424" SIZE PANELS AND BELOW SHALL BE PACKAGED IN AN ENVELOPE WITH NO METAL (CLASP)
 - 7. ALL "3020" SIZE PANELS AND ABOVE SHALL BE PACKAGED IN CARDBOARD WITH NO METAL (STAPLES)

SPECIAL REQUIREMENTS

- ASSEMBLY:**
- 1. SWING PANEL KIT INCLUDES THE FOLLOWING:
 - (1) ALUMINUM SWING PANEL (RMAH1010SP)
 - (1) SWING PANEL MOUNT KIT (ATAHSPM)

NEMA 250: TYPE N/A IEC 60529: N/A		STANDARD P/N: AH1010SPK		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03	XXX ± 0.010
COLOR: N/A COLOR STANDARD: N/A		CUSTOMER DWG:		<div><div>AttaBox®</div><div>A BRAND OF ROBROY ENCLOSURES®</div></div> <div>Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378</div>					
MATERIAL: 3003-H14 ALUMINUM									
REVISION HISTORY									
REV	DESCRIPTION	DATE	ENG						
-	-	-	-						
-	-	-	-	WWW.ATTABOX.COM		DRAWN BY		DATE	CUSTOMER
-	-	-	-	AA		02/06/18			
-	-	-	-	SCALE		DESCRIPTION		PART NUMBER	
-	-	-	-	DO NOT SCALE		STANDARD SWING PANEL KIT		ATAH1010SPK	
-	-	-	-					DWG AH1010SPK	

THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2018 ROBROY ENCLOSURES



Robroy Enclosures
500 Maple Street
Belding, Michigan 48809
Phone: 616-794-0700
Fax: 616-749-3378