



FOR REFERENCE ONLY
SWING PANEL MOUNTS SHOWN AS INSTALLED

- NOTES:**
- PANEL SHALL BE FREE FROM BURRS & SHARP EDGES
 - PANEL SHALL BE FLAT
 - MISALIGNED EDGES EXCEEDING 0.005" (STEPS) SHALL NOT BE PERMITTED
 - ALL EDGES SHALL BE SQUARE AND PARALLEL
 - PANEL SHALL HAVE CLEAR PVC FILM ON ONE SIDE
 - ALL "2424" SIZE PANELS AND BELOW SHALL BE PACKAGED IN AN ENVELOPE WITH NO METAL (CLASP)
 - ALL "3020" SIZE PANELS AND ABOVE SHALL BE PACKAGED IN CARDBOARD WITH NO METAL (STAPLES)

THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED. UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2016 ROBROY ENCLOSURES

SPECIAL REQUIREMENTS

1. SWING PANEL KIT INCLUDES THE FOLLOWING:
 -(1) ALUMINUM SWING PANEL (RMAH2424SP)
 -(1) SWING PANEL MOUNT KIT (ATAHSPM)

NEMA 250: TYPE N/A IEC 60529: N/A		STANDARD P/N: AH2424SPK	ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED	.XX ± 0.03 .XXX ± 0.010
COLOR: N/A COLOR STANDARD: N/A		CUSTOMER DWG:	 AttaBox A ROBROY ENCLOSURES™ BRAND Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378			
MATERIAL: 3003-H14 ALUMINUM						
REVISION HISTORY						
REV	DESCRIPTION	DATE	ENG	DRAWN BY	DATE	CUSTOMER
-	-	-	-	DRH	08/31/16	
-	-	-	-	SCALE		
-	-	-	-	DO NOT SCALE		
DESCRIPTION STANDARD SWING PANEL KIT			PART NUMBER ATAH2424SPK			

DWG
AH2424SPK