



THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED. UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2020 ROBROY ENCLOSURES.

SPECIAL REQUIREMENTS

MOLDING:
1. PROTECTIVE MYLAR FILM SHALL BE APPLIED TO TOP OF COVER

ASSEMBLY:
1. (1) POLYCARBONATE ACCESSORY KIT (WPPCACOKIT) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE

HARDWARE INCLUDED:
-(6) 1/4-20 x 1/2 FLAT HEAD PHILLIPS MACHINE SCREW (RMSC1/4-20X.5FLPH)
-(4) #10-32 x 5/8 PAN HEAD PHILLIPS MACHINE SCREW (RMSC10/32X5/8SS)
-(4) #10-32 x 3/8 PAN HEAD SCREW (RMSC10/32X3/8ZN)
-(4) #10 WASHER (RMWAS10ZN)
2. (1) STYROFOAM SHEET SHALL BE PLACED ON TOP OF COVER INSIDE CARTON

NEMA 250: TYPE 1, 3R, 4, 4X, 12 IEC 60529: IP66				STANDARD P/N: AH10106CSS		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03		.XXX ± 0.010	
COLOR: N/A COLOR STANDARD: PANTONE 7541 C				CUSTOMER DWG:		<div><div>AttaBox™</div><div>Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-704-0700 Fax: 616-749-3378</div><div>DWG AH10106CSS</div></div>							
MATERIAL: POLYCARBONATE													
REVISION HISTORY													
REV	DESCRIPTION			DATE	ENG								
-	-			-	-								
-	-			-	-								
-	-			-	-								
-	-			-	-								
-	-			-	-								
-	-			-	-								
-	-			-	-								
-	-			-	-								
				SCALE DO NOT SCALE		DESCRIPTION STANDARD ENCLOSURE		PART NUMBER ATAH10106CSS					

AttaBox

Robroy Enclosures
500 Maple Street
Belding, Michigan 48809
Phone: 616-794-0700
Fax: 616-749-3378

DRAWN BY AA	DATE 8/15/20	CUSTOMER	DWG AH10106CSS
SCALE DO NOT SCALE	DESCRIPTION STANDARD ENCLOSURE	PART NUMBER ATAH10106CSS	