








SECTION A-A



FOR REFERENCE ONLY
MOUNTING FEET SHOWN AS INSTALLED




SECTION B-B



THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED. UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2016 ROBROY ENCLOSURES

- SPECIAL REQUIREMENTS**
- ASSEMBLY:
- (1) ACCESSORY KIT (ATAHAK) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE
- HARDWARE INCLUDED:
- (4) #1/4-20 x 1/2 FLAT HEAD PHILLIPS MACHINE SCREW (RMSC1/4-20X.5FLPH)
 - (4) #10-32 x 5/8 PAN HEAD PHILLIPS MACHINE SCREW (RMSC10/32X5/8SS)
 - (4) #10-32 x 3/8 PAN HEAD SCREW (RMSC10/32X3/8ZN)
 - (4) #10 WASHER (RMWAS10ZN)
- (1) STYROFOAM SHEET SHALL BE PLACED ON TOP OF COVER INSIDE CARTON

| | | | | | | | | | | |
|--|-------------|------|------------------------|--------------------|--|--|--------------------------------|--|---------------|-----------------|
| NEMA 250: TYPE 1, 3R, 4, 4X, 6P, 12 IEC 60529: IP66, IP68 | | | STANDARD P/N: AH16148C | | ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED | | TOLERANCES UNLESS SPECIFIED | | .XX ± 0.03 | .XXX ± 0.010 |
| COLOR: N/A COLOR STANDARD: PANTONE 7541 C | | | CUSTOMER DWG: | | <div><div></div><div>AttaBox A ROBROY ENCLOSURES™ BRAND</div></div> <div>Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378</div> | | | | | |
| MATERIAL: POLYCARBONATE | | | | | | | | | | |
| REVISION HISTORY | | | | | | | | | | |
| REV | DESCRIPTION | DATE | ENG | | | | | | | |
| - | - | - | - | | | | | | | |
| - | - | - | - | DRAWN BY | | | | | | |
| - | - | - | - | AJC | | | | | | |
| - | - | - | - | DATE | | | | | | |
| - | - | - | - | 11/23/16 | | | | | | |
| - | - | - | - | CUSTOMER | | | | | | |
| - | - | - | - | | | | | | | |
| - | - | - | - | SCALE | | | | | | |
| - | - | - | - | DO NOT SCALE | | | | | | |
| | | | | DESCRIPTION | PART NUMBER | | | | | |
| | | | | STANDARD ENCLOSURE | ATAH16148C | | | | | |



Robroy Enclosures
500 Maple Street
Belding, Michigan 48809
Phone: 616-794-0700
Fax: 616-749-3378