

SECTION A-A


SECTION B-B

FOR REFERENCE ONLY
MOUNTING FEET SHOWN AS INSTALLED

THIS DRAWING IS THE SOLE AND EXCLUSIVE
PROPERTY OF ROBROY ENCLOSURES.
NO PART OF THIS DRAWING MAY BE
REPRODUCED, DISTRIBUTED, OR PUBLICALLY
DISPLAYED IN ANY FORM OR BY ANY MEANS
WITHOUT THE EXPRESS WRITTEN
PERMISSION OF ROBROY ENCLOSURES.
ALL RIGHTS RESERVED
UNDER THE COPYRIGHT LAWS.
COPYRIGHT © 2017 ROBROY ENCLOSURES

ASSEMBLY:
1. MOUNTING FEET SHOWN AS INSTALLED - FOR REFERENCE ONLY
- SOLD SEPARATELY
- CENTURION SERIES MOUNTING FOOT KIT (FECLMTGFTKIT)
- INCLUDES (4) 5/16-18 x 1/2 FLAT HEAD SLOTTED SCREWS (RMSCS16-18X1/2FL)
2. (1) CENTURION SERIES SCREW PACK (WP4PKBP) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE
HARDWARE INCLUDED:
- (4) #10-32 x 3/8 PAN HEAD SCREW (RMSC1032X3/8ZN)
- (4) #10 WASHER (RMWAS10ZN)

SPECIAL REQUIREMENTS

NEMA 250: TYPE 1, 3, 3S, 3R, 4X, 12 IEC 60529: N/A				STANDARD P/N: CE1109HPL		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03		XXX ± 0.010	
COLOR: GLACIER GREY (WPR3X13) COLOR STANDARD: PANTONE 428 C				CUSTOMER DWG:									
MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)													
REVISION HISTORY						Robroy Enclosures 600 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378							
REV	DESCRIPTION			DATE	ENG	DWG							
-	-			-	-	CE1109HPL							
-	-			-	-								
-	-			-	-								
-	-			-	-								
-	-			-	-								
-	-			-	-								
-	-			-	-								
WWW.ATTABOX.COM													
DRAWN BY		DATE		CUSTOMER									
E91		05/17/17											
SCALE		DESCRIPTION		PART NUMBER									
DO NOT SCALE		STANDARD ENCLOSURE		ATCE1109HPL									



Robroy Enclosures
500 Maple Street
Belding, Michigan 48809
Phone: 616-794-0700
Fax: 616-749-3378

DWG
CE1109HPL