



FOR REFERENCE ONLY
MOUNTING FEET SHOWN AS INSTALLED

SPECIAL REQUIREMENTS

- ASSEMBLY:
- 1. MOUNTING FEET SHOWN AS INSTALLED - FOR REFERENCE ONLY
 - SOLD SEPARATELY
 - FREEDOM SERIES MOUNTING FOOT KIT (FEFRMGFTKIT)
 - INCLUDES (4) #10-32 x 7/16 FLAT HEAD PHILLIPS HEAD SCREWS (RMSC10-32X7/16FHPH)
 - 2. (1) FREEDOM SERIES SCREW PACK (WP2PKFRBP) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE
 - HARDWARE INCLUDED:
 - (2) #10-32 x 1-1/4 PAN HEAD COMBINATION DRIVE SCREW (RMSC10-32X1-1/4COM)
 - (4) #10-32 x 3/8 PAN HEAD SCREW (RMSC10-32X3/8ZN)
 - (4) #10 WASHER (RMWAS10ZN)
 - (2) O-RING FOR COVER SCREW(RMAS568007)

THIS DRAWING IS THE SOLE AND EXCLUSIVE
PROPERTY OF ROBROY ENCLOSURES.
NO PART OF THIS DRAWING MAY BE
REPRODUCED, DISTRIBUTED, OR PUBLICALLY
DISPLAYED IN ANY FORM OR BY ANY MEANS
WITHOUT THE EXPRESS WRITTEN
PERMISSION OF ROBROY ENCLOSURES.
ALL RIGHTS RESERVED
UNDER THE COPYRIGHT LAWS.
COPYRIGHT © 2017 ROBROY ENCLOSURES

END USER NOTES:
1. TORQUE COVER SCREWS TO 20-24 IN.-LBS. TO MAINTAIN RATINGS

NEMA 250: TYPE 1, 3, 3S, 4X, 12, 13 IEC 60529: IP66 COLOR: GLACIER GREY (WPR3X13) COLOR STANDARD: PANTONE 428 C			STANDARD P/N: FR141206HW		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03		XXX ± 0.010	
MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)					<div>AttaBox</div> <div>Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378</div>							
REVISION HISTORY												
REV	DESCRIPTION			DATE								
-	-			-	-	<div>WWW.ATTABOX.COM</div> <div>DRAWN BY: DATE</div> <div>E91 05/10/17</div> <div>CUSTOMER</div> <div>DWG FR141206HW</div>						
-	-			-	-							
-	-			-	-							
-	-			-	-							
-	-			-	-							
-	-			-	-	<div>SCALE</div> <div>DO NOT SCALE</div> <div>DESCRIPTION STANDARD ENCLOSURE</div> <div>PART NUMBER ATFR141206HW</div>						
-	-			-	-							
-	-			-	-							