




EXTENDED VIEW



RETRACTED VIEW



ISOMETRIC VIEW



M4 X 0.7 THREAD  
(8-32 UNF-2A OPTIONAL)

ALLIANCE SENSORS INDUCTIVE LINEAR POSITION SENSOR, SLIDE, 150MM STROKE, 4MM SHAFT DIAMETER, 0-10 VDC OUTPUT, 12.7MM DIAMETER X 165.1MM BODY, M4 X 0.7 MOUNT, PIGTAIL, 3.2FT/1M CABLE LENGTH.

**LZE13-150A-00-10S**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
**[mm]**

LATEST VERSION  
3/22/2022

SHEET 1 OF 1