







- 1 = TRANSMITTER DIODE  
2 = RECEIVER DIODE  
3 = SCREW M3 - 0.5 Nm



ISOMETRIC VIEW



NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.  
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

OPT2172
Units: mm [inches] Scale: Full WENGLOR PHOTOELECTRIC LASER SENSOR, DIFFUSE WITH BACKGROUND SUPPRESSION, 32 X 22 X 12MM, CLASS 1 LASER LIGHT EMISSION, 0- 1M SENSING DISTANCE, 10-30 VDC OPERATING VOLTAGE, PNP, IO-LINK COMPATIBLE, 4-PIN M8 QUICK-DISCONNECT
